



DuraForm[®] ProX[®] GF Plastic

A rigid, heat-resistant, glass-filled plastic for use with ProX SLS 500 product series and ideal for functional parts.

General Properties

MEASUREMENT	CONDITION	METRIC	U.S.
Sintered Part Density	Internal	1.33 g/cm ³	1.33 g/cm ³

Mechanical Properties

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength, Ultimate	D638	45 MPa	6550 psi
Tensile Modulus	D638	3720 MPa	540 ksi
Elongation at Break	D638	2.8 %	2.8 %
Flexural Strength	D790	60 MPa	8930 psi
Flexural Modulus	D790	3120 MPa	450 ksi
Hardness, Shore D	D2240	73	73
Impact Strength (notched Izod, 23 °C) @0.12"	D256	48 J/m	0.90 ft-lb/in
Impact Strength (unnotched Izod, 23 °C) @0.12"	D256	207 J/m	3.88 ft-lb/in

* All data generated using 3D Systems recommended recycle rates

Thermal Properties

MEASUREMENT	CONDITION	METRIC	U.S.
HDT @ 0.45 MPa	D648	180 °C	356 °F
HDT @ 1.82 MPa	D648	129 °C	264 °F
Coefficient of Thermal Expansion (0-50 °C)	E831	85.3 µm/m-°C	47.4 µin/in-°F
Coefficient of Thermal Expansion (85-145 °C)	E831	173.7 µm/m-°C	96.5 µin/in-°F
Specific Heat Capacity	E1269	1.26 J/g-°C	0.3 BTU/lb-°F
Thermal Conductivity	E1530	0.33 W/m-K	2.29 BTU-in/hr-ft ² -°F
Flammability 3.0 mm	UL94	HB	HB
Impact Strength (unnotched Izod, 23 °C) @0.12"	D256	207 J/m	3.88 ft-lb/in

Electrical Properties

MEASUREMENT	CONDITION	METRIC	U.S.
Volume Resistivity (Ω-cm)	D257	7.20 x 10 ¹⁴	7.20 x 10 ¹⁴
Surface Resistivity (Ω/sq)	D257	2.76 x 10 ¹⁴	2.76 x 10 ¹⁴
Dissipation Factor, 1 KHz	D150	0.051	0.051
Dielectric Constant, 1 KHz	D150	3.31	3.31
Dielectric Strength	D149	18.1 kV/mm	460 kV/in

Features

- Glass-filled composite
- Best in class rigidity and stiffness
- Excellent surface finish and resolution
- Improved thermal resistance versus unfilled materials

Benefits

- Replace molded and CNC-machined glass and mineral-filled plastic articles for short-run production
- Fuel and oil resistance make it perfect for automotive and aerospace applications
- Easy to process

Applications

Automotive/under the hood, intake manifolds and other rigid high-temperature components, aerospace/aviation, enclosures, cases and covers, power tools and small engine components, jigs and fixtures, thermoforming and hydroforming.



www.3dsystems.com

UK
Tel: +44 1442 282 600

**Germany, Scandinavia,
Eastern Europe, Middle East**
Tel: +49 6151 357 0

USA
Tel: +1 803.326.3900

Asia-Pacific
Melbourne Tel: +61 3 9819 4422
Sydney Tel: +61 2 9516 5571

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2016 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems and DuraForm are registered trademarks and the 3D Systems logo is a trademark of 3D Systems, Inc.