

Figure 4[™] FLEX-BLK 20

Flexible, Durable

Durable, flexible, high impact-resistant material with long-term environmental stability

Figure 4®

FATIGUE RESISTANT BLACK PLASTIC, WITH LOOK AND FEEL OF PRODUCTION POLYPROPYLENE

Figure 4 FLEX-BLK 20 is a flexible, high impact-resistant material for extremely durable black parts with look and feel of production polypropylene. Great for functional prototypes, enclosures and assemblies, as well as short-run production parts, this fatigue resistant material provides outstanding flexibility and accuracy, enabling many applications.

Liquid Material

MEASUREMENT	CONDITION	METRIC	U.S.	
Viscosity	@ 25 °C (77 °F)	2250 cps	5440 lb/ft-hr	
Color		Black		
Liquid Density	@ 25 °C (77 °F)	1.11 g/cm ³	0.040 lb/in ³	
Package Volume		1 kg bottle - Figure 4 Standalone 2.5 kg cartridge - Figure 4 Modular 10 kg container - Figure 4 Production		
Layer Thickness (Standard Mode)		0.05 mm	0.002 in	
Vertical Build Speed Standard Mode Draft Mode		25 mm/hr 29 mm/hr	1 in/hr 1.1 in/hr	

APPLICATIONS

- Functional assemblies and prototypes
 Automotive styling parts
 - Consumer goods and electronic components
 - Containers and enclosures
 - Product design
- Master patterns for RTV/silicone molding
- Concept and marketing models

BENEFITS

- Reliable and robust functional prototypes
- Excellent mechanical properties and accuracy
- Beautiful black parts with look and feel of molded black polypropylene
- Improved environmental stability of mechanical and performance properties over time

FEATURES

- High elongation at break and notched impact strength
- Lower tensile modulus
- Engineered for long term environmental stability
- Easy to clean





Post-Cured Material

MECHANICAL PROPERTIES						
MEASUREMENT	CONDITION	METRIC	U.S.			
Solid Density (g/cm3 lb/in ³)	ASTM D792	1.18	0.043			
Tensile Strength, Ultimate (MPa PSI)	ASTM D638	36	5220			
Tensile Strength, at Yield (MPa PSI)	ASTM D638	24	3480			
Tensile Modulus (MPa KSI)	ASTM D638	840	122			
Elongation at Break	ASTM D638	86%				
Elongation at Yield	ASTM D638	7.5%				
Flexural Strength (MPa PSI)	ASTM D790	22	3190			
Flexural Modulus (MPa KSI)	ASTM D790	680	99			
Notched Izod Impact Strength (J/m Ft-lbs/in)	ASTM D256	91	1.7			
Unnotched Izod Impact Strength (J/m Ft-lbs/in)	ASTM D4812	Did not break				
Heat Deflection Temperature @ 0.45 MPa (66 PSI) @ 1.82 MPa (264 PSI)	ASTM D648	41 °C <25 °C	106 °F <77 °F			
Coefficient of Thermal Expansion (CTE) (ppm/°C ppm/°F) < Tg > Tg	ASTM E831	69 188	38 104			
Glass Transition (Tg), DMA, E"	ASTM E1640	11 °C	52 °F			
Hardness, Shore	ASTM D2240	68D				
Water Absorption (24 hour)	ASTM D570	0.64%				

3D SYSTEMS

www.3dsystems.com

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

@ 2019 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo and Figure 4 are registered trademarks of 3D Systems, Inc.

* Note: Not all products and materials are available in all countries – please consult your local sales representative for availability.

3DS-40112A