

# Figure 4<sup>™</sup> PRO-BLK 10

Production-grade additive manufacturing material with game-changing thermoplastic-like mechanical properties and long-term environmental stability

## **Production Rigid**

Figure 4®

### VERSATILE RIGID HEAT RESISTANT MATERIAL COMBINES SPEED, STRENGTH, EXCELLENT MECHANICAL PROPERTIES FOR TOOL-LESS, DIRECT PRODUCTION OF PLASTIC PARTS

Figure 4 PRO-BLK 10 delivers on the promise of additive manufacturing with true direct digital production of plastic parts. Go from CAD to manufacturing line in one day with tool-less, same day part production. With a fast print speed and simplified post-processing that includes a single curing cycle and single solvent cleaning, this material delivers exceptional throughput. It is a high precision resin producing parts with a smooth surface finish and sidewall quality, and has excellent mechanical properties and long-term environmental stability that brings a new level of assurance to 3D production.

#### Liquid Material

MEASUREMENT	CONDITION	METRIC	U.S.	
Viscosity	@ 25 °C (77 °F)	293 cps	709 lb/ft-hr	
Color		Black		
Liquid Density	@ 25 °C (77 °F)	1.07 g/cm <sup>3</sup>	0.039 lb/in <sup>3</sup>	
Package Volume		1 kg bottle - Figure 4 Standalone 2.5 kg cartridge - Figure 4 Modular 10 kg container - Figure 4 Production		
Layer Thickness (Standard Mode)		0.05 mm	0.02 in	
Vertical Build Speed Standard Mode Draft Mode		62 mm/hr 81 mm/hr	2.4 in/hr 3.2 in/hr	

#### **APPLICATIONS**

- Tool-less, same day production
- Direct production of small black plastic parts; examples include: motor housings, connectors, snap-fits, automotive interior and other general-use parts
- Digital production to replace injection molding or soft tooling processes

#### **BENEFITS**

- Improved environmental stability of mechanical and performance properties over time
- Fast throughput for part-in-hand with no secondary thermal cure required
- Simple, single solvent cleaning
- Excellent surface quality and repeatability
- Accurate, low distortion material for fast first article print success

#### **FEATURES**

- Fast print speed up to 62 mm/hr at 50 micron layer thickness
- 70 °C heat deflection temperature,
  12% elongation at break
- Durability and strength





#### **Post-Cured Material**

MECHANICAL PROPERTIES						
MEASUREMENT	CONDITION	METRIC	U.S.			
Solid Density (g/cm³   lb/in³)	ASTM D792	1.16	0.042			
Tensile Strength, Ultimate (MPa   PSI)	ASTM D412	63	9140			
Tensile Strength, at Yield (MPa   PSI)	ASTM D412	63	9140			
Tensile Modulus (MPa   KSI)	ASTM D412	2320	336			
Elongation at Break	ASTM D412	12%				
Elongation at Yield	ASTM D412	4.7%				
Flexural Strength (MPa   PSI)	ASTM D790	92	13340			
Flexural Modulus (MPa   KSI)	ASTM D790	2290	332			
Notched Izod Impact Strength (J/m   Ft-lbs/in)	ASTM D256	24	0.5			
Unnotched Izod Impact Strength (J/m   Ft-lbs/in)	ASTM D4812	614	11.5			
Glass Transition (Tg), DMA, E"	ASTM E1640	62 °C	144 °F			
Heat Deflection Temperature @ 0.45 MPa (66 PSI) @ 1.82 MPa (264 PSI)	ASTM D648	70 °C 56 °C	158 °F 133 °F			
Coefficient of Thermal Expansion (CTE) (ppm/°C   ppm/°F) < Tg > Tg	ASTM E831	<b>71</b> 188	39 104			
Hardness, Shore	ASTM D2240	79D				
Water Absorption (24 hour)	Absorption (24 hour) ASTM D570 1.16%		6%			





www.3dsystems.com

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2019 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo and Figure 4 are registered trademarks of 3D Systems, Inc.

\* Note: Not all products and materials are available in all countries – please consult your local sales representative for availability.

3DS-40113A 09-19