

# Cocuchas De Michoacán Historical Vase Reproduction

Mexico-based foundry Fundidora Morelia and pattern shop PSSI collaborate using large-format pellet extrusion 3D printing with EXT 1070 Titan Pellet to reproduce iconic pieces of local art.

Using the latest in production additive manufacturing and 3D scanning techniques, patterns for the historic vases were produced quickly and cost effectively.

#### History

Fundidora Morelia (FM) is a family-owned steel foundry with more than 40 years of experience specializing in the casting of ferrous alloys. Proveedora de Servicios y Suministros Industriales (PSSI), was founded in 2016 to serve as a high-tech pattern shop for FM. Together, the companies utilize 3D printers, including a 3D Systems EXT 1070 Titan Pellet 3D printer, CNC routers, 3D laser scanning, CAD modeling and the latest testing techniques to create highquality patterns and castings.

The small town of Cochuco, located in the state of Michoacan, Mexico, is well known for its history and craftmanship, where local artisans most notably manufacture giant clay pots by hand.

"As a family from Michoacan and as an enterprise based in Morelia, we are very proud of our culture and traditions, and we wanted to make a tribute to our artisans and their renewed arts and crafts," said Alonso Alvarez of PSSI.

# CHALLENGE:

Produce large, custom patterns for unique casting project without the longer lead times of traditional pattern-making methods, while keeping costs competitive.

## SOLUTION:

Leverage 3D Systems' EXT 1070 Titan Pellet large-format 3D printer with high- throughput pellet extrusion to quickly and cost effectively produce the custom patterns.

#### **RESULTS:**

Time to and labor produce patterns cut in half due to lights-out manufacturing enabled by the EXT 1070 Titan Pellet.



FM and PSSI commissioned a joint effort to reproduce two of the iconic giant vases in cast steel, bridging the industrial and artisanal sectors of the region.

## Process

PSSI conducted the reverse engineering process by 3D scanning the original pot and creating 3D-printable CAD models of the cope and drag patterns for casting. PSSI printed the large patterns using pellet extrusion on their EXT 1070 Titan Pellet 3D printer and hand finished the parts with body filler and sanding for a smooth finish.

FM cast the model in steel which they gave a blued finish, and stainless steel which they polished to a striking mirror finish. The time to produce the patterns was cut in half with 3D printing compared to traditional methods of CNC machining the patterns. It took just 1.5 days to create the patterns on the EXT 1070 Titan Pellet. Thanks to the EXT 1070's lights out manufacturing, labor requirements were also cut in half compared to traditional pattern making methods.

#### **DETAILS:**

- Print Time: 13 hours
- Feedstock: PETG Pellets
- Material Weight: 88 lbs total
- Nozzle Size: 2mm
- Layer Height: 1mm





**3D Systems Corporation** 333 Three D Systems Circle Rock Hill, SC 29730 www.3dsystems.com Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2023 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, ProJet, VisiJet and 3D Sprint are registered trademarks of 3D Systems, Inc.